



HTG911H

Power supply 24V DC 2,5A at 70°C

Technical characteristics

Configuration

Number of modules 4

Main electrical features

Rated operational voltage Ue 196 / 264 V

Type of supply voltage AC

Voltage

Output voltage 24 V DC

Rated operational voltage in DC 0 V

Electric current

Output intensity 2.5 A

Output intensity 2.5 A

Dimensions

Depth of installed product 63 mm

Height of installed product 93 mm

Installation height 0 m

Width of installed product 71 mm

Frequency

Frequency 50 to 60 Hz

Power

Power absorbed 60 W

Total power loss under IN 6 W

Installation, mounting

Suitable for busbar mounting No

Suitable for front mounting No

Connection

Connection cross-section of input and output with screws, for massive conductors 1 / 2.5 mm²

Connection cross section of access and exit with screws, for flexible conductor 0.75 / 2.5 mm²

Type of connection Screw connection

Equipment

Short-circuit protected Yes

Standards

European directive RoHs	compliant
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...70 °C
Storage/transport temperature	-40...85 °C
