



HMJ400DR

**Moulded Case Circuit Breaker h3 x630 TM ADJ 3P3D 400A 50kA FTC**

**Technical characteristics**

**Architecture**

Type of order	Toggle
Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3P3D
Fixing mode	fixing plate
Type of case	Fixed built-in

**Functions**

Complete device with protection unit	Yes
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	TM A/A
Integrated earth fault protection	No

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Main electrical features**

Rated operational voltage Ue	220 / 415 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

**Electric current**

Rated current	400 A
Thermal protection nob setting xIN	0.63 / 0.8 / 1
Rating current 10°C according to IEC 60947	470.7 A
Rating current 15°C according to IEC 60947	462.5 A
Rating current 20°C according to IEC 60947	454.1 A
Rating current 25°C according to IEC 60947	445.5 A
Rating current 30°C according to IEC 60947	436.8 A

Rating current 35°C according to IEC 60947	427.9 A
Rating current 40°C according to IEC 60947	418.8 A
Rating current 45°C according to IEC 60947	409.5 A
Rating current 50°C according to IEC 60947	400 A
Rating current 55°C according to IEC 60947	390.3 A
Rating current 60°C according to IEC 60947	380.3 A
Rating current 65°C according to IEC 60947	370 A
Rating current 70°C according to IEC 60947	359.4 A
Breaking capacity on 1 pole for IT 230V NF 60947-2	10 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	10 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	10 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA
Range of the thermal adjustment	250 / 300 / 400 A
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	50 kA
<b>Dimensions</b>	
Depth of installed product	150 mm
Height of installed product	260 mm
Width of installed product	140 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Power loss per pole at 0.63*In	15.3 W
Power loss per pole at 0.8*In	24.7 W
Total power loss at 0.63*In	46 W
Total power loss at 0.8*In	74.2 W
Total power loss under IN	116 W
Power loss per pole at In	38.7 W
<b>Tripping</b>	
Time of response when opening	10 ms
<b>Installation, mounting</b>	
Tightening torque	18Nm
DIN rail mounting with optional adaptor	No
Suitable for front mounting	No
Suitable for ground mounting	Yes

Subject to technical modifications

**Connection**

Connection	Front connection
Type of connection	Terminal

**Protection**

Instantaneous protection (Ii): type	fixed
-------------------------------------	-------

**Cable**

Cable Material	Cu
----------------	----

**Settings**

Range of the magnetic adjustment	2000 / 2400 / 2800 / 3200 / 3600 / 4000 A
Magnetic protection nob setting xIN	5 / 6 / 7 / 8 / 9 / 10

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes
Can be accessorized	Yes

**Use cases**

Category of use	A
-----------------	---

**Standards**

Standard text	IEC 60947-2
European directive WEEE	concerned

**Safety**

Protection index IP	IP4X
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m

**temperatur**

Temperature of calibration	50 °C
----------------------------	-------