



HXA027H

**Alarm contact NO-NC right side (x630/P630)**

**Technical characteristics**

**Architecture**

|             |         |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

**Main electrical features**

|                              |       |
|------------------------------|-------|
| Rated operational voltage Ue | 250 V |
|------------------------------|-------|

**Voltage**

|                                 |        |
|---------------------------------|--------|
| Rated impulse withstand voltage | 1500 V |
|---------------------------------|--------|

|                                 |       |
|---------------------------------|-------|
| Rated operational voltage in DC | 125 V |
|---------------------------------|-------|

**Electric current**

|               |     |
|---------------|-----|
| Rated current | 3 A |
|---------------|-----|

**Power**

|                           |     |
|---------------------------|-----|
| Total power loss under IN | 3 W |
|---------------------------|-----|

**Connection**

|                  |              |
|------------------|--------------|
| Type of contacts | 1 changeover |
|------------------|--------------|

**Equipment**

|   |   |
|---|---|
| Number of auxiliary contacts as normally closed contact | 1 |
|---|---|

|   |   |
|---|---|
| Number of auxiliary contacts as normally open contact | 1 |
|---|---|

|   |   |
|---|---|
| Number of auxiliary contacts as change-over contact | 0 |
|---|---|

|  |   |
|--|---|
| Number of auxiliary contacts as fault signal | 2 |
|--|---|

**Standards**

|                         |                      |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
|-------------------------|----------------------|

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|