



JK1B104F2

125A TPN BOARD,INVICTA,10+4WAY,FLUSH,FOR 50 OC TESTING

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Configuration

Number of modules	0
-------------------	---

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Dimensions

Insertion depth	120 mm
Depth of installed product	5 mm
Internal depth	117 mm
Height of installed product	960 mm
Width of installed product	470 mm
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.2 mm
Identification od protection index	41
Interlockable	No
Door locking	with special tool
Transparent cover or door	No

Materials

Colour	light grey
Material	Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	26
--------------------------	----

Equipment

Quantity of rails	0
Extension possible	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety	
Protection index IP	IP41
Protection class	isol.class I