



JK1B12F2

**125A TPN BOARD, INVICTA, 12WAY, FLUSH, FOR 50 OC TESTING**

**Technical characteristics**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Configuration**

Number of modules	0
-------------------	---

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Dimensions**

Insertion depth	120 mm
Depth of installed product	5 mm
Internal depth	117 mm
Height of installed product	740 mm
Width of installed product	470 mm
Thickness of sidewall material	1.2 mm

**Cover, door**

Material thickness cover	1.2 mm
Identification od protection index	41
Interlockable	No
Door locking	with special tool
Transparent cover or door	No

**Materials**

Colour	light grey
Material	Steel

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	26
Number of accessible phases	3

**Equipment**

With energy meter	No
Quantity of rails	0
Can be accessorized	Yes
With bell transformer	No
Extension possible	Yes

Subject to technical modifications

With socket	No
-------------	----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP41
Protection class	isol.class I
RoHS conform	Yes