



HMT200DR

**Moulded Case Circuit Breaker h3+ P250 TM ADJ 3P3D 200A 50kA FTC**

**Technical characteristics**

**Architecture**

Type of order	Toggle
Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3P3D
Type of case	Fixed built-in

**Functions**

Complete device with protection unit	Yes
Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	TM A/A
Integrated earth fault protection	No

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Main electrical features**

Rated operational voltage Ue	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

**Electric current**

Rated current	200 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	6 kA
Thermal protection nob setting xIN	0.63 / 0.8 / 1
Rating current 10°C according to IEC 60947	263.8 A
Rating current 15°C according to IEC 60947	256.7 A
Rating current 20°C according to IEC 60947	249.4 A
Rating current 25°C according to IEC 60947	241.9 A

Rating current 30°C according to IEC 60947	234.1 A
Rating current 35°C according to IEC 60947	226.1 A
Rating current 40°C according to IEC 60947	217.7 A
Rating current 45°C according to IEC 60947	209 A
Rating current 50°C according to IEC 60947	200 A
Rating current 55°C according to IEC 60947	190.5 A
Rating current 60°C according to IEC 60947	180.5 A
Rating current 65°C according to IEC 60947	170 A
Rating current 70°C according to IEC 60947	158.7 A
Rated service breaking capacity Ics under 660V AC according IEC 60947-2	6 kA
Breaking capacity on 1 pole for IT 230V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 690V NF 60947-2	4.25 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA
Range of the thermal adjustment	125 / 160 / 200 A
Rated service breaking capacity Ics under 110-138V AC according IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 660V AC IEC 60947-2	6 kA
<b>Dimensions</b>	
Depth of installed product	97 mm
Height of installed product	165 mm
Width of installed product	105 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Power loss per pole at 0.63*In	4.69 W
Power loss per pole at 0.8*In	7.68 W
Total power loss at 0.63*In	14.06 W
Total power loss at 0.8*In	23.04 W
Total power loss under IN	36 W
Power loss per pole at In	12 W
<b>Tripping</b>	

Subject to technical modifications

Short-time delayed tripping	No
<b>Endurance</b>	
Electric endurance in number of cycles	10000
Number of mechanical operations	40000
<b>Cover, door</b>	
Interlockable	Yes
<b>Installation, mounting</b>	
Tightening torque	12Nm
DIN rail mounting with optional adaptor	No
Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes
<b>Connection</b>	
Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 185mm <sup>2</sup>
Connection	Front connection
Type of connection	Terminal
<b>Protection</b>	
Instantaneous protection (Ii): type	without
<b>Cable</b>	
Cable Material	Cu / Al
<b>Settings</b>	
Range of the magnetic adjustment	1200 / 1600 / 2000 / 2400 A
Magnetic protection nob setting xIN	6 / 8 / 10 / 12
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes
Can be accessorized	Yes
<b>Use cases</b>	
Category of use	A
<b>Use</b>	
Vibrations and shocks withstand	IEC 68068-2-52 Test FC
<b>Standards</b>	
Standard text	IEC 60947-2
<b>Safety</b>	

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

---

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Air humidity protection	95%HR 55°C sev Kn (IEC 68-2-30/52)

---

**temperatur**

Temperature of calibration	50 °C
----------------------------	-------