



KB263C

## Insulated busbar 2P 63A prong 10mm<sup>2</sup> 24M

### Technical characteristics

#### Architecture

|                 |     |
|-----------------|-----|
| Number of poles | 2 P |
| Type of pole    | 2 P |

#### Configuration

|                   |    |
|-------------------|----|
| Number of modules | 24 |
|-------------------|----|

#### Compatibility

|  |                 |
|--|-----------------|
| Intended for the compatible references | Modular devices |
|--|-----------------|

#### Main electrical features

|                              |             |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 / 400 V |
|------------------------------|-------------|

#### Voltage

|                                 |       |
|---------------------------------|-------|
| Max operating voltage           | 400 V |
| Rated impulse withstand voltage | 4 kV  |

#### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

#### Dimensions

|                                   |         |
|-----------------------------------|---------|
| Length                            | 420 mm  |
| Pitch                             | 17.8 mm |
| Fixation distance in module steps | 2       |

#### Power supply

|                                       |          |
|---------------------------------------|----------|
| Number of phases for the power supply | 2 phases |
|---------------------------------------|----------|

#### Installation, mounting

|  |    |
|--|----|
| Suitable to a device with an auxiliary | No |
|--|----|

#### Connection

|  |                   |
|--|-------------------|
| Connection cross-sect. rigid cable       | 10mm <sup>2</sup> |
| Suitable for product with neutral busbar | Yes               |
| Connector type                           | busbar prong      |
| Type of connection                       | with screw        |

#### Equipment

|                                  |    |
|----------------------------------|----|
| Number of appliances to build in | 12 |
|----------------------------------|----|

#### Safety

|               |    |
|---------------|----|
| REACH conform | No |
|---------------|----|

RoHS conform

Yes

**Use conditions**

---

Insulated

Yes