



HMW401JR

Moulded Case Circuit Breaker h3+ P630 LSI 4P4D N0-50-100% 400A 50kA FTC

Technical characteristics

Architecture

| | |
|---------------------------|----------------|
| Neutral position | left |
| Number of protected poles | 4 |
| Number of poles | 4 P |
| Type of case | Fixed built-in |

Functions

| | |
|--|-----|
| Complete device with protection unit | Yes |
| Version as main switch | Yes |
| Version as emergency stop installation | No |
| Version as safety switch | No |
| Version as maintenance-/service switch | Yes |
| Trip Unit | LSI |
| Integrated earth fault protection | No |
| Concurrently switching N-neutral | Yes |

Controls and indicators

| | |
|------------------------|----|
| Motor drive integrated | No |
|------------------------|----|

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 220 / 690 V |
| Type of supply voltage | AC |
| Frequency | 50/60 Hz |

Voltage

| | |
|---------------------------------|-------|
| Rated insulation voltage | 800 V |
| Rated impulse withstand voltage | 8 kV |
| With under voltage release | No |

Electric current

| | |
|--|-------|
| Rated current | 400 A |
| Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2 | 12 kA |
| Rating current 10°C according to IEC 60947 | 400 A |
| Rating current 15°C according to IEC 60947 | 400 A |
| Rating current 20°C according to IEC 60947 | 400 A |
| Rating current 25°C according to IEC 60947 | 400 A |
| Rating current 30°C according to IEC 60947 | 400 A |
| Rating current 35°C according to IEC 60947 | 400 A |
| Rating current 40°C according to IEC 60947 | 400 A |

| | |
|--|-------|
| Rating current 45°C according to IEC 60947 | 400 A |
| Rating current 50°C according to IEC 60947 | 400 A |
| Rating current 55°C according to IEC 60947 | 400 A |
| Rating current 60°C according to IEC 60947 | 400 A |
| Rating current 65°C according to IEC 60947 | 400 A |
| Rating current 70°C according to IEC 60947 | 400 A |
| Rated service breaking capacity Ics under 660V AC according IEC 60947-2 | 12 kA |
| Breaking capacity on 1 pole for IT 230V NF 60947-2 | 10 kA |
| Breaking capacity on 1 pole for IT 400V NF 60947-2 | 10 kA |
| Breaking capacity on 1 pole for IT 415V NF 60947-2 | 10 kA |
| Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2 | 85 kA |
| Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2 | 85 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2 | 50 kA |
| Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2 | 50 kA |
| Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2 | 85 kA |
| Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2 | 50 kA |
| Rated ultimate short-circuit breaking capacity Icu under 660V AC IEC 60947-2 | 12 kA |

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 150 mm |
| Height of installed product | 260 mm |
| Width of installed product | 185 mm |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|--------------------------------|--------|
| Power loss per pole at 0.63*In | 12 W |
| Power loss per pole at 0.8*In | 19.2 W |
| Total power loss at 0.63*In | 36 W |
| Total power loss at 0.8*In | 57.6 W |
| Total power loss under IN | 90 W |
| Power loss per pole at In | 30 W |

Tripping

| | |
|-------------------------------|-------|
| Time of response when opening | 10 ms |
|-------------------------------|-------|

Installation, mounting

| | |
|---|-----|
| DIN rail mounting with optional adaptor | No |
| Suitable for front mounting | No |
| Suitable for ground mounting | Yes |

Connection

Subject to technical modifications

| | |
|--|-------------|
| Type of connection | Terminal |
| Cable | |
| Cable Material | Cu |
| Equipment | |
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact | 0 |
| Number of auxiliary contacts as change-over contact | 0 |
| Motor drive optional | Yes |
| Can be accessorized | Yes |
| Use cases | |
| Category of use | B |
| Standards | |
| Standard text | IEC 60947-2 |
| European directive WEEE | concerned |
| Use conditions | |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Altitude | 2000 m |
| temperatur | |
| Temperature of calibration | 50 °C |