



**Insulated busbar 3P 80A Prong 16mm<sup>2</sup> 57M**

**Technical characteristics**

**Architecture**

Number of poles	3 P
Type of pole	3 P

**Configuration**

Number of modules	57
-------------------	----

**Compatibility**

Intended for the compatible references	Modular devices
----------------------------------------	-----------------

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

**Voltage**

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	80 A
---------------	------

**Dimensions**

Length	1000 mm
Pitch	17.8 mm
Fixation distance in module steps	3

**Power supply**

Number of phases for the power supply	3-phase
---------------------------------------	---------

**Installation, mounting**

Suitable to a device with an auxiliary	No
----------------------------------------	----

**Connection**

Connection cross-sect. rigid cable	16mm <sup>2</sup>
Suitable for product with neutral busbar	No
Connector type	busbar prong
Type of connection	with screw

**Equipment**

Number of appliances to build in	19
----------------------------------	----

**Safety**

REACH conform	No
---------------	----

KB380B

RoHS conform

Yes

**Use conditions**

---

Insulated

Yes