



KD163B



Insulated busbar 1P 63A fork 10mm² 57M

Technical characteristics

Architecture

| | |
|-----------------|-----|
| Number of poles | 1 P |
| Type of pole | 1 P |

Compatibility

| | |
|----------------------------------------|-----------------|
| Intended for the compatible references | Modular devices |
|----------------------------------------|-----------------|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 415 V |
|------------------------------|-------|

Voltage

| | |
|-----------------------|-------|
| Max operating voltage | 230 V |
|-----------------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Dimensions

| | |
|-----------------------------------|---------|
| Length | 1000 mm |
| Pitch | 17.8 mm |
| Fixation distance in module steps | 1 |

Installation, mounting

| | |
|----------------------------------------|----|
| Suitable to a device with an auxiliary | No |
|----------------------------------------|----|

Connection

| | |
|------------------------------------------|-------------------|
| Connection cross-sect. rigid cable | 10mm ² |
| Suitable for product with neutral busbar | No |
| Connector type | busbar fork |
| Type of connection | with screw |

Equipment

| | |
|----------------------------------|------|
| Number of connections | 57 C |
| Number of appliances to build in | 57 |

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

Use conditions

