



KD263B

**Insulated busbar 2P 63A fork 10mm<sup>2</sup> 57M**

**Technical characteristics**

**Architecture**

|                 |     |
|-----------------|-----|
| Number of poles | 2 P |
| Type of pole    | 3 P |

**Compatibility**

|  |                 |
|--|-----------------|
| Intended for the compatible references | Modular devices |
|--|-----------------|

**Main electrical features**

|                              |             |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 / 400 V |
|------------------------------|-------------|

**Voltage**

|                       |       |
|-----------------------|-------|
| Max operating voltage | 400 V |
|-----------------------|-------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Dimensions**

|                                   |         |
|-----------------------------------|---------|
| Length                            | 1000 mm |
| Pitch                             | 17.8 mm |
| Fixation distance in module steps | 2       |

**Installation, mounting**

|  |    |
|--|----|
| Suitable to a device with an auxiliary | No |
|--|----|

**Connection**

|  |                   |
|--|-------------------|
| Connection cross-sect. rigid cable       | 10mm <sup>2</sup> |
| Suitable for product with neutral busbar | Yes               |
| Connector type                           | busbar fork       |
| Type of connection                       | with screw        |

**Equipment**

|                                  |    |
|----------------------------------|----|
| Number of appliances to build in | 28 |
|----------------------------------|----|

**Standards**

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |

**Use conditions**

|           |     |
|-----------|-----|
| Insulated | Yes |
|-----------|-----|