



L50600



Fuse carrier 1P+N 32A 400V L38 1M

Technical characteristics

Architecture

Number of poles	2 P
Type of pole	1P+N
Fixing mode	DIN rail type O (symmetrical)

Configuration

Number of modules	1
-------------------	---

Electric current

Rated current	32 A
Rating current of fuse cartridge	2 / 4 / 6 / 8 / 10 / 12 / 16 / 20 / 25 / 32 A

Fuse

CharactFuse	gG
-------------	----

Dimensions

Depth of installed product	75 mm
Height of installed product	77 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	1.5 W
---------------------------	-------

Cover, door

Interlockable	No
---------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C