



LF312G

**Cylindrical fuse-links for industrial applications 10x38mm gG 12A 500V AC 120kA**

**Technical characteristics**

**Functions**

Release characteristic fuses	Time-lag
------------------------------	----------

**Main electrical features**

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
Rated operational voltage $U_e$	500 V
Type of supply voltage	AC

**Electric current**

Rated current	12 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2	120 kA

**Fuse**

CharactFuse	gG
Fuse Size	10.3 x 38

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under $I_N$	1.3 W
------------------------------	-------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes