



HNA040Z

Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 40A 40kA CTC

Technical characteristics

Architecture

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3P3D

Functions

Trip Unit	TM F/F
Integrated earth fault protection	No
Concurrently switching N-neutral	No

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	40 A
Thermal protection nob setting xIN	1
Rating current 10°C according to IEC 60947	49.5 A
Rating current 15°C according to IEC 60947	48.4 A
Rating current 20°C according to IEC 60947	47.3 A
Rating current 25°C according to IEC 60947	46.1 A
Rating current 30°C according to IEC 60947	45 A
Rating current 35°C according to IEC 60947	43.8 A
Rating current 40°C according to IEC 60947	42.5 A
Rating current 45°C according to IEC 60947	41.3 A
Rating current 50°C according to IEC 60947	40 A
Rating current 55°C according to IEC 60947	38.6 A
Rating current 60°C according to IEC 60947	37.2 A
Rating current 65°C according to IEC 60947	35.7 A
Rating current 70°C according to IEC 60947	34.2 A

Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	40 kA
Range of the thermal adjustment	40 A
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	40 kA
Dimensions	
Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	75 mm
Frequency	
Frequency	50 to 60 Hz
Power	
Total power loss under IN	11 W
Power loss per pole at In	3.7 W
Endurance	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
Connection	
Type of connection	with screw
Settings	
Range of the magnetic adjustment	600 A
Equipment	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes
Standards	
Standard text	IEC 60947-2
European directive WEEE	concerned
Safety	
Protection index IP	IP4X
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	

Subject to technical modifications

Altitude

2000 m

temperatur

Temperature of calibration

50 °C