



LF408G

### Industrial fuse-links 14x51 gG 8A

#### Technical characteristics

#### Functions

|                              |          |
|------------------------------|----------|
| Release characteristic fuses | Fast (F) |
|------------------------------|----------|

#### Main electrical features

|  |       |
|--|-------|
| Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1 | 80 kA |
|--|-------|

|                                 |       |
|---------------------------------|-------|
| Rated operational voltage $U_e$ | 690 V |
|---------------------------------|-------|

|                        |    |
|------------------------|----|
| Type of supply voltage | AC |
|------------------------|----|

#### Electric current

|               |     |
|---------------|-----|
| Rated current | 8 A |
|---------------|-----|

|  |       |
|--|-------|
| Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2 | 80 kA |
|--|-------|

#### Fuse

|             |    |
|-------------|----|
| CharactFuse | gG |
|-------------|----|

|           |         |
|-----------|---------|
| Fuse Size | 14 x 51 |
|-----------|---------|

#### Frequency

|           |             |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

#### Power

|                              |     |
|------------------------------|-----|
| Total power loss under $I_N$ | 1 W |
|------------------------------|-----|

#### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

|              |     |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|