



LF410M

## Industrial fuse-links 14x51 aM 10A

### Technical characteristics

#### Functions

|                              |          |
|------------------------------|----------|
| Release characteristic fuses | Time-lag |
|------------------------------|----------|

#### Main electrical features

|  |       |
|--|-------|
| Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1 | 80 kA |
| Rated operational voltage $U_e$  | 690 V |
| Type of supply voltage   | AC    |

#### Electric current

|  |       |
|--|-------|
| Rated current  | 10 A  |
| Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2 | 80 kA |

#### Frequency

|           |             |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

#### Power

|                              |        |
|------------------------------|--------|
| Total power loss under $I_N$ | 0.53 W |
|------------------------------|--------|

#### Standards

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

#### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | Yes |