



LS512



Fuse carrier 1P+N 32A 690V L38 2M

Technical characteristics

Architecture

Number of poles	2 P
Type of pole	1P+N

Configuration

Number of modules	2
-------------------	---

Main electrical features

Type of supply voltage	AC
------------------------	----

Voltage

Rated insulation voltage	690 V
--------------------------	-------

Electric current

Rated current	32 A
---------------	------

Dimensions

Depth of installed product	75 mm
Height of installed product	83 mm
Width of installed product	36 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	4 W
---------------------------	-----

Installation, mounting

Tightening torque	2,2Nm
-------------------	-------

Equipment

Can be accessorized	Yes
---------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-5...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C