



LS670

**Microswitch 1P for fuse carrier L51**

**Technical characteristics**

**Architecture**

Number of poles 1 P

**Configuration**

Number of modules 0.5

**Compatibility**

Suitable for Fuse carrier

**Main electrical features**

Rated operational voltage Ue 220 / 250 V

**Voltage**

Rated insulation voltage 6000 V

Rated operational voltage in DC 24 V

**Electric current**

Acceptable current rating with AC1 5 A

I<sub>min</sub> = f (U = 230 V AC) 5 A

**Fuse**

Fuse Size 14 x 51

**Dimensions**

Depth of installed product 20 mm

Height of installed product 35 mm

Width of installed product 35 mm

**Equipment**

Quantity of NC contacts 0

Quantity of NO contacts 0

Quantity of INV contacts 1

**Standards**

European directive WEEE concerned

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Operating temperature	-5...40 °C
Air humidity protection	95% / 80°C
Storage/transport temperature	-25...55 °C