




HNW400JR



Moulded Case Circuit Breaker h3+ P630 LSI 3P3D 400A 40kA FTC

Technical characteristics

Architecture

Type of order	Toggle
Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3P3D
Type of case	Fixed built-in

Functions

Complete device with protection unit	Yes
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	LSI
With integrated earth leakage fault protection	No

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features


Rated operational voltage Ue	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	400 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	7 kA
Rating current 10°C according to IEC 60947	400 A
Rating current 15°C according to IEC 60947	400 A
Rating current 20°C according to IEC 60947	400 A
Rating current 25°C according to IEC 60947	400 A
Rating current 30°C according to IEC 60947	400 A



Rating current 35°C according to IEC 60947	400 A
Rating current 40°C according to IEC 60947	400 A
Rating current 45°C according to IEC 60947	400 A
Rating current 50°C according to IEC 60947	400 A
Rating current 55°C according to IEC 60947	400 A
Rating current 60°C according to IEC 60947	400 A
Rating current 65°C according to IEC 60947	400 A
Rating current 70°C according to IEC 60947	400 A
Rated service breaking capacity Ics under 660V AC according IEC 60947-2	7 kA
Breaking capacity on 1 pole for IT 230V NF 60947-2	10 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	10 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	10 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 660V AC IEC 60947-2	7 kA
Dimensions	
Depth of installed product	150 mm
Height of installed product	260 mm
Width of installed product	140 mm
Frequency	
Frequency	50 to 60 Hz
Power	
Power loss per pole at 0.63*In	7.5 W
Power loss per pole at 0.8*In	12.4 W
Total power loss at 0.63*In	22.6 W
Total power loss at 0.8*In	37 W
Total power loss under IN	57.8 W
Power loss per pole at In	19.3 W
Tripping	
Time of response when opening	10 ms
Installation, mounting	
Tightening torque	18Nm
DIN rail mounting with optional adaptor	No

Subject to technical modifications

Suitable for front mounting	No
Suitable for ground mounting	Yes
Connection	
Connection	Front connection
Type of connection	Terminal
Cable	
Cable Material	Cu
Equipment	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes
Can be accessorized	Yes
Use cases	
Category of use	B
Standards	
Standard text	IEC 60947-2
Safety	
REACH conform	No
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
temperatur	
Temperature of calibration	50 °C