



HR520

## EARTH LEAKAGE RELAY 0.03-10A TIME DELAY 50% LED

### Technical characteristics

#### Configuration

Number of modules	3
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	230 V
---------------------------------	-------

#### Voltage

Max operating voltage	276 V
-----------------------	-------

#### Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A / 10 A
----------------------------------	---

Torroids : Allowed overload	30kA / 100ms
-----------------------------	--------------

#### Power

Power consumed	5 VA
----------------	------

#### Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1 / 2,5mm <sup>2</sup>
---	------------------------

Connection cross-sect. rigid cable	1,5 / 4mm <sup>2</sup>
------------------------------------	------------------------

Connection cross-section in flexible cable for the measurement	1 / 2.5 mm <sup>2</sup>
--	-------------------------

Connection cross-section in massive cable for the measurement	1.5 / 4 mm <sup>2</sup>
---	-------------------------

#### Settings

Time delay of residual current	0 / 0.1 / 0.3 / 0.4 / 0.5 / 1 / 3 s
--------------------------------	-------------------------------------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP30
---------------------	------

Residual current type	A
-----------------------	---

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Altitude	2000 m
----------	--------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------