



MM502N



**Motor protection circuit breaker 3P 0.16-0.25A ; 0.03/0.06 kW at 230/415V 230/41**

**Technical characteristics**

**Architecture**

Type of order	Short thumb-grip
Number of poles	3 P
Type of pole	3 P

**Configuration**

Number of modules	2.5
-------------------	-----

**Main electrical features**

Rated operational voltage Ue	690 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V

**Electric current**

Rated current	0.25 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	150 kA
Magnetic regulating current	12.4 / 15.5 / 18.6 In
Thermal trip setting with 30°	0.16 / 0.17 / 0.18 / 0.19 / 0.21 / 0.22 / 0.23 / 0.24 / 0.25 A
Rating current 0°C according to IEC 60947	0.25 A
Rating current 10°C according to IEC 60947	0.25 A
Rating current 20°C according to IEC 60947	0.25 A
Rating current 30°C according to IEC 60947	0.25 A
Rating current 40°C according to IEC 60947	0.25 A
Rating current 50°C according to IEC 60947	0.25 A
Rated service breaking capacity Ics AC according to IEC 60947-2	100 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	150 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	150 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	150 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	150 kA

Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	150 kA
--	--------

### Dimensions

Strip length of main circuit connections	10 mm
--	-------

### Frequency

Frequency	50 to 60 Hz
-----------	-------------

### Power

Total power loss under IN	5.15 W
---------------------------	--------

Standard power rating of 3 phase motor in AC3 under 400V	0.06 kW
--	---------

Rated operational power for 3P under 415V AC3 according IEC60947-4	0.06 kW
--	---------

Rated operational power for 3P under 440V AC3 according IEC60947-4	0.06 kW
--	---------

Rated operational power for 3P under 500V AC3 according IEC60947-4	0.06 kW
--	---------

### Electrical specifications

Nominal tightening torque of main circuit	1.7 Nm
---	--------

### Endurance

Electric endurance in number of cycles	50000
--	-------

Mechanical endurance in number of operations per hour	40
---	----

Number of mechanical operations	100000
---------------------------------	--------

### Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Type connection of power circuit	with screw
----------------------------------	------------

### Connection

Connection cross-section of input and output with screws, for massive conductors	1 / 6 mm <sup>2</sup>
--	-----------------------

Connection cross section of access and exit with screws, for flexible conductor	1 / 6 mm <sup>2</sup>
---	-----------------------

Cable flexibel cross section for main circuit	1x (1 - 6) mm <sup>2</sup> / 2x (1 - 6) mm <sup>2</sup>
---	---

Cable rigid cross section for main circuit	1x (1 - 6) mm <sup>2</sup> / 2x (1 - 6) mm <sup>2</sup>
--	---

Type of connection	with screw
--------------------	------------

### Settings

min/maxi threshold value of the AC magnetic operation	3.1 / 4.7 A
---	-------------

Setting type In or Ith	IN
------------------------	----

### Equipment

Automatic compensation of the temperature	-5 / 40 °C
---	------------

Can be accessorized	Yes
---------------------	-----

### Use cases

Category of use	AC3
-----------------	-----

### Standards

Subject to technical modifications

---

Standard text

IEC 60947-4-1 ; EN 60947-4-1

---

European directive RoHS

voluntary compliance

---

**Safety**

---

REACH conform

Yes

---

RoHS conform

Yes

---

Halogen free

No

---

Phase failure sensitive

Yes

---

**Use conditions**

---

Operating temperature

-25...55 °C

---

Degree of pollution according to IEC 60664 /  
IEC 60947-2

3

---

Storage/transport temperature

-25...80 °C

---

**temperatur**

---

Temperature of calibration

30 °C