



HXT049H

Motor Operator P250 48VDC without Auto-Reset

Technical characteristics

Architecture

Type of order motor drive

Main electrical features

Type of supply voltage DC

Voltage

DC control voltage 48 V

Command voltage AC 0 V

Electric current

Inrush current OFF-RESET 48V DC - 17A

Inrush current ON 48V DC - 12A

Operating current OFF-RESET 48V DC - 12A

Operating current ON 48V DC - 12A

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Altitude 2000 m