



JK1B066S2

**125A TPN BOARD,INVICTA,6+6WAY,SURFACE,FOR 50 OC TESTING**

**Technical characteristics**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Configuration**

Number of modules	0
-------------------	---

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Dimensions**

Insertion depth	120 mm
Depth of installed product	125 mm
Internal depth	117 mm
Height of installed product	775 mm
Width of installed product	445 mm
Thickness of sidewall material	1.2 mm

**Cover, door**

Material thickness cover	1.2 mm
Identification od protection index	41
Interlockable	No
Door locking	with special tool
Transparent cover or door	No

**Materials**

Colour	light grey
Material	Steel

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	26
--------------------------	----

**Equipment**

Quantity of rails	0
Extension possible	Yes

**Safety**

IK protection code against mechanical impacts	IK05
---	------

Protection index IP	IP41
Protection class	isol.class I
RoHS conform	Yes