



JK1B08S2

125A TPN BOARD,INVICTA,8WAY,SURFACE,FOR 50 OC TESTING

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Configuration

Number of modules	0
-------------------	---

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Dimensions

Insertion depth	120 mm
Depth of installed product	125 mm
Internal depth	117 mm
Height of installed product	605 mm
Width of installed product	445 mm
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.2 mm
Identification od protection index	41
Interlockable	No
Door locking	with special tool
Transparent cover or door	No

Materials

Colour	light grey
Material	Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	26
Number of accessible phases	3

Equipment

With energy meter	No
Quantity of rails	0
Can be accessorized	Yes
With bell transformer	No
Extension possible	Yes

Subject to technical modifications

With socket	No
Standards	
European directive WEEE	concerned
Safety	
Protection index IP	IP41
Protection class	isol.class I