



JK1B24S2

**125A TPN BOARD, INVICTA, 24WAY, SURFACE, FOR 50 OC TESTING**

**Technical characteristics**

**Architecture**

Fixing mode surface-mounting

**Configuration**

Number of modules 0

**Compatibility**

Suitable for lightning protection No

**Dimensions**

Insertion depth 120 mm

Depth of installed product 125 mm

Internal depth 117 mm

Height of installed product 1105 mm

Width of installed product 445 mm

Thickness of sidewall material 1.2 mm

**Cover, door**

Material thickness cover 1.2 mm

Identification of protection index 41

Interlockable No

Door locking with special tool

Transparent cover or door No

**Materials**

Colour light grey

Material Steel

**Installation, mounting**

Suitable for outdoor use No

**Connection**

Number of conduit inlets 26

**Equipment**

Quantity of rails 0

Extension possible Yes

**Safety**

Protection index IP IP41

Protection class isol.class I