



MU163A

MCB 1P 63A C-63A 1M

Technical characteristics

Architecture

Neutral position	not applicable
Number of protected poles	1
Number of poles	1 P
Type of pole	1 P
Fixing mode	Din-Rail
Curve	C

Functions

Concurrently switching N-neutral	No
----------------------------------	----

Configuration

Number of modules	1
-------------------	---

Connectivity

Top connection alignment for modular devices	Aligned terminal
Bottom connection alignment for modular devices	Aligned terminal

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	6 kA
Rated operational voltage U_e	230 / 400 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated current	63 A
Rated service breaking capacity I_{cs} AC according IEC 60898-1	6 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 I_n
Magnetic regulating current	5 / 10 I_n
min/maxi threshold value of the DC magnetic operation	5 / 15 I_n
min/maxi threshold value of the DC thermal operation	1.13 / 1.45 I_n

Breaking capacity on 1 pole for IT 400V NF 60947-2	3 kA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	6 kA
Rated service breaking capacity Ics AC according IEC 60947-2	75 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	10 kA

Electric current / temperature

Rating current -25°C	81.1 A
Rating current -20°C	79.6 A
Rating current -15°C	78.1 A
Rating current -10°C	76.6 A
Rating current -5°C	75 A
Rating current 0°C	73.4 A
Rating current 5°C	71.8 A
Rating current 10°C	70.1 A
Rating current 15°C	68.4 A
Rating current 20°C	66.7 A
Rating current 25°C	64.9 A
Rating current 30°C	63 A
Rating current 35°C	62.8 A
Rating current 40°C	62.6 A
Rating current 45°C	62.3 A
Rating current 50°C	62.1 A
Rating current 55°C	61.9 A
Rating current 60°C	61.7 A
Rating current 65°C	61.4 A
Rating current 70°C	61.2 A

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85
Correction factor of magnetic tripping with 100 Hz	1.1
Correction factor of magnetic tripping with 200 Hz	1.2
Correction factor of magnetic tripping with 400 Hz	1.5
Correction factor of magnetic tripping with 60 Hz	1

Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Subject to technical modifications

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	7.4 W
Power loss per pole at In	7.4 W

Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

Installation, mounting

Type of top connection for modular devices	with screw
Tightening torque	2,8Nm
Type of top rail clip for modular devices	NA
Type of bottom rail clip for modular devices	metallic
Type of Bottom Connection for modular devices	Blconnect
Top removability for modular devices	No
Bottom removability for modular devices	No

Connection

Connection cross-section of input and output with screws, for massive conductors	1 / 35 mm ²
Connection cross section of access and exit with screws, for flexible conductor	1 / 25 mm ²

Equipment

Quick connect	no
With transparent product label holder	No

Standards

Standard text	IEC 60898-1
European directive WEEE	concerned

Safety

Protection index IP	IP20
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-25...70 °C
Class of energy limitation I ² t	3
Altitude	2000 m
Storage/transport temperature	-25...80 °C