



KDN280B

Insulated busbar 2P 80A fork 16mm² 57M

Technical characteristics

Architecture

| | |
|-----------------|-----|
| Number of poles | 2 P |
| Type of pole | 2 P |

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 / 400 V |
|------------------------------|-------------|

Voltage

| | |
|-----------------------|-------|
| Max operating voltage | 400 V |
|-----------------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 80 A |
|---------------|------|

Dimensions

| | |
|--------|---------|
| Length | 1000 mm |
| Pitch | 17.8 mm |

Installation, mounting

| | |
|--|----|
| Suitable to a device with an auxiliary | No |
|--|----|

Connection

| | |
|--|----------------------------|
| Connection cross-sect. rigid cable | 16mm ² |
| Suitable for product with neutral busbar | Yes |
| Connector type | busbar fork |
| Type of connection | with screw / quick connect |

Equipment

| | |
|----------------------------------|----|
| Number of appliances to build in | 27 |
|----------------------------------|----|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Use conditions

| | |
|-----------|-----|
| Insulated | Yes |
|-----------|-----|