



L12801



**Fuse carrier 1P+N 32A 400V 1M**

**Technical characteristics**

**Architecture**

Type of pole	1P+N
Fixing mode	DIN rail type O (symmetrical)

**Configuration**

Number of modules	1
-------------------	---

**Electric current**

Rated current	32 A
Rating current of fuse cartridge	32 A

**Fuse**

CharactFuse	B
Fuse Size	10.3 x 38

**Dimensions**

Depth of installed product	75 mm
Height of installed product	77 mm
Width of installed product	17.5 mm

**Power**

Total power loss under IN	1.5 W
---------------------------	-------

**Cover, door**

Interlockable	No
---------------	----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
REACH conform	No

**Use conditions**

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C