



LF406M

**Industrial fuse-links 14x51 aM 6A**

**Technical characteristics**

**Functions**

|                              |          |
|------------------------------|----------|
| Release characteristic fuses | Time-lag |
|------------------------------|----------|

**Main electrical features**

|  |       |
|--|-------|
| Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1 | 80 kA |
| Rated operational voltage $U_e$  | 690 V |
| Type of supply voltage   | AC    |

**Electric current**

|  |       |
|--|-------|
| Rated current  | 6 A   |
| Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2 | 80 kA |

**Fuse**

|             |         |
|-------------|---------|
| CharactFuse | gG ; aM |
| Fuse Size   | 14 x 51 |

**Frequency**

|           |             |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

**Power**

|                              |        |
|------------------------------|--------|
| Total power loss under $I_N$ | 0.42 W |
|------------------------------|--------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | Yes |