



LS503



**Fuse 3P 32A 690V L38 3M**

**Technical characteristics**

**Architecture**

Number of poles	3 P
Type of pole	3 P

**Configuration**

Number of modules	3
-------------------	---

**Main electrical features**

Type of supply voltage	AC
------------------------	----

**Voltage**

Rated insulation voltage	690 V
--------------------------	-------

**Electric current**

Rated current	32 A
---------------	------

**Fuse**

CharactFuse	gG ; aM
Fuse Size	10.3 x 38

**Dimensions**

Depth of installed product	75 mm
Height of installed product	83 mm
Width of installed product	54 mm

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under IN	11.1 W
---------------------------	--------

**Installation, mounting**

Tightening torque	2,2Nm
-------------------	-------

**Equipment**

Can be accessorized	Yes
---------------------	-----

**Use conditions**

Operating temperature	-5...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C