



LS670

## Microswitch 1P for fuse carrier L51

### Technical characteristics

#### Architecture

Number of poles	1 P
-----------------	-----

#### Configuration

Number of modules	0.5
-------------------	-----

#### Compatibility

Suitable for	Fuse carrier
--------------	--------------

#### Main electrical features

Rated operational voltage Ue	220 / 250 V
------------------------------	-------------

#### Voltage

Rated insulation voltage	6000 V
Rated operational voltage in DC	24 V

#### Electric current

Acceptable current rating with AC1	5 A
I <sub>min</sub> = f (U = 230 V AC)	5 A

#### Dimensions

Depth of installed product	20 mm
Height of installed product	35 mm
Width of installed product	35 mm

#### Equipment

Quantity of NC contacts	0
Quantity of NO contacts	0
Quantity of INV contacts	1

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Operating temperature	-5...40 °C
Storage/transport temperature	-25...55 °C