



LS771

**Microswitch 3P for fuse carrier L58**

**Technical characteristics**

**Architecture**

Number of poles 3 P

**Configuration**

Number of modules 0.5

**Compatibility**

Suitable for Fuse carrier

**Main electrical features**

Rated operational voltage  $U_e$  220 / 250 V

**Voltage**

Rated insulation voltage 6000 V

Rated operational voltage in DC 24 / 220 V

**Electric current**

Acceptable current rating with AC1 5 A

$I_{min} = f(U = 230 \text{ V AC})$  5 A

**Dimensions**

Width of installed product 9 mm

**Equipment**

Quantity of NC contacts 0

Quantity of NO contacts 0

Quantity of INV contacts 1

**Standards**

European directive WEEE concerned

**Use conditions**

Operating temperature -5...40 °C

Storage/transport temperature -25...55 °C