



MZ527N



## Alarm contact for motor starter 2C

### Technical characteristics

#### Architecture

Maximum poles of the main device	3
----------------------------------	---

#### Configuration

Number of modules	0.5
-------------------	-----

#### Main electrical features

Rated operational voltage Ue	220 / 500 V
Type of supply voltage	AC
Frequency	40/60 Hz

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V
Rated operational voltage in DC	24 / 220 V

#### Electric current

Acceptable current rating with AC1	3 A
Simulation fault current	No
Maximum current	25 A
Rated current	1 A
I <sub>min</sub> = f (U = 230 V AC)	3 A
I <sub>min</sub> = f (U = 230 V DC)	0.25 A
I <sub>min</sub> =f(U=400V AC) for power circuit	2 A
I <sub>min</sub> =f(U=24V DC) for power circuit	2 A

#### Dimensions

Depth of installed product	68 mm
Width of installed product	9 mm

#### Power

Total power loss under I <sub>N</sub>	0.2 W
Power loss per pole at I <sub>n</sub>	0.1 W

#### Endurance

Electric endurance in number of cycles	5000
Number of mechanical operations	10000

#### Installation, mounting

Tightening torque	1,3Nm
Factory fitted	No

**Connection**

Connection cross-sect. flexible conductor	2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	2,5mm <sup>2</sup>
Type of contacts	2NO
Type of connection	with screw

**Accessories included**

Type of accessory	fault-signal contact
-------------------	----------------------

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	2
Number of auxiliary contacts as change-over contact	0
Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0
Number of auxiliary contacts as fault signal	2

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-25...55 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Air humidity protection	95% / 80°C
Storage/transport temperature	-25...80 °C