



MCN125A

MCB 1P 6kA C-25A 1M

Technical characteristics

Architecture

| | |
|---------------------------|-----|
| Number of protected poles | 1 |
| Number of poles | 1 P |
| Type of pole | 1 P |
| Curve | C |

Functions

| | |
|----------------------------------|----|
| Concurrently switching N-neutral | No |
|----------------------------------|----|

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Connectivity

| | |
|---|------------------|
| Top connection alignment for modular devices | Aligned terminal |
| Bottom connection alignment for modular devices | Aligned terminal |

Main electrical features

| | |
|--|-------------|
| Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 | 6 kA |
| Rated operational voltage U_e | 230 / 400 V |
| Type of supply voltage | AC |
| Frequency | 50/60 Hz |

Voltage

| | |
|---------------------------------|--------|
| Rated insulation voltage | 500 V |
| Rated impulse withstand voltage | 4000 V |

Electric current

| | |
|---|-------------------|
| Rated current | 25 A |
| Rated service breaking capacity I_{cs} AC according IEC 60898-1 | 6 kA |
| min/maxi threshold value of the AC thermal operation | 1.13 / 1.45 I_n |
| Magnetic regulating current | 5 / 10 I_n |
| min/maxi threshold value of the DC magnetic operation | 5 / 15 I_n |
| min/maxi threshold value of the DC thermal operation | 1.13 / 1.45 I_n |
| Breaking capacity on 1 pole for IT 400V NF 60947-2 | 3 kA |
| Rated short circuit breaking capacity I_{cn} under 230V AC according IEC60898-1 | 6 kA |

| | |
|--|-------------|
| Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2 | 10 kA |
| Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2 | 10 kA |
| Electric current / temperature | |
| Rating current -25°C | 33.4 A |
| Rating current -20°C | 32.6 A |
| Rating current -15°C | 31.8 A |
| Rating current -10°C | 31 A |
| Rating current -5°C | 30.3 A |
| Rating current 0°C | 29.5 A |
| Rating current 5°C | 28.7 A |
| Rating current 10°C | 28 A |
| Rating current 15°C | 27.2 A |
| Rating current 20°C | 26.4 A |
| Rating current 25°C | 25.7 A |
| Rating current 30°C | 25 A |
| Rating current 35°C | 24.1 A |
| Rating current 40°C | 23.4 A |
| Rating current 45°C | 22.6 A |
| Rating current 50°C | 21.8 A |
| Rating current 55°C | 21.1 A |
| Rating current 60°C | 20.3 A |
| Rating current 65°C | 19.5 A |
| Rating current 70°C | 18.8 A |
| Current correction factors | |
| Correction factor of rating current for 2 devices placed side-by-side | 1 |
| Correction factor of rating current for 3 devices placed side-by-side | 0.95 |
| Correction factor of rating current for 4 and 5 devices placed side-by-side | 0.9 |
| Correction factor of rating current for 6 devices placed side-by-side | 0.85 |
| Correction factor of magnetic tripping with 100 Hz | 1.1 |
| Correction factor of magnetic tripping with 200 Hz | 1.2 |
| Correction factor of magnetic tripping with 400 Hz | 1.5 |
| Correction factor of magnetic tripping with 60 Hz | 1 |
| Dimensions | |
| Depth of installed product | 70 mm |
| Height of installed product | 83 mm |
| Width of installed product | 17.5 mm |
| Frequency | |
| Frequency | 50 to 60 Hz |

| | |
|--|------------------------|
| Power | |
| Total power loss under IN | 3 W |
| Power loss per pole at In | 3 W |
| Endurance | |
| Electric endurance in number of cycles | 10000 |
| Number of mechanical operations | 20000 |
| Installation, mounting | |
| Type of top connection for modular devices | with screw |
| Tightening torque | 2,8Nm |
| Type of Bottom Connection for modular devices | Blconnect |
| Connection | |
| Connection cross-sect. flexible conductor | 1 / 25mm ² |
| Connection cross-sect. rigid cable | 1 / 35mm ² |
| Connection cross-section of input and output with screws, for massive conductors | 1 / 35 mm ² |
| Connection cross section of access and exit with screws, for flexible conductor | 1 / 25 mm ² |
| Standards | |
| Standard text | EN 60898-1 |
| European directive WEEE | concerned |
| Safety | |
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |
| Use conditions | |
| Operating temperature | -25...70 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Class of energy limitation I ² t | 3 |
| Altitude | 2000 m |
| Air humidity protection | for all climates |
| Storage/transport temperature | -25...80 °C |