



MCN325



MCB 3P 6kA C-25A 3M

Technical characteristics

Architecture

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3 P
Curve	C

Functions

Concurrently switching N-neutral	No
----------------------------------	----

Configuration

Number of modules	3
-------------------	---

Connectivity

Top connection alignment for modular devices	Aligned terminal
Bottom connection alignment for modular devices	Aligned terminal

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	6 kA
Rated operational voltage U_e	415 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated current	25 A
Rated service breaking capacity I_{cs} AC according IEC 60898-1	6 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 I_n
Magnetic regulating current	5 / 10 I_n
Rated short circuit breaking capacity I_{cn} under 400V AC according IEC60898-1	6 kA

Electric current / temperature

Rating current -25°C	31.5 A
Rating current -20°C	31 A

Rating current -15°C	30.5 A
Rating current -10°C	29.9 A
Rating current -5°C	29.3 A
Rating current 0°C	28.8 A
Rating current 5°C	28.2 A
Rating current 10°C	27.6 A
Rating current 15°C	26.9 A
Rating current 20°C	26.3 A
Rating current 25°C	25.7 A
Rating current 30°C	25 A
Rating current 35°C	24.3 A
Rating current 40°C	23.5 A
Rating current 45°C	22.7 A
Rating current 50°C	21.9 A
Rating current 55°C	21.1 A
Rating current 60°C	20.2 A
Rating current 65°C	19.3 A
Rating current 70°C	18.3 A

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.8
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.7
Correction factor of rating current for 6 devices placed side-by-side	0.6
Correction factor of magnetic tripping with 100 Hz	1.1
Correction factor of magnetic tripping with 200 Hz	1.2
Correction factor of magnetic tripping with 400 Hz	1.5
Correction factor of magnetic tripping with 60 Hz	1

Dimensions

Depth of installed product	70 mm
Height of installed product	84.6 mm
Width of installed product	52.5 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	10.1 W
Power loss per pole at In	3.45 W

Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

Subject to technical modifications

Installation, mounting

Type of top connection for modular devices	with screw
Tightening torque	2,8Nm
Type of top rail clip for modular devices	NA
Type of bottom rail clip for modular devices	plastic
Type of Bottom Connection for modular devices	Blconnect
Top removability for modular devices	No
Bottom removability for modular devices	Yes

Connection

Connection cross-sect. flexible conductor	1 / 25mm ²
Connection cross-sect. rigid cable	1 / 35mm ²
Connection cross-section of input and output with screws, for massive conductors	1 / 35 mm ²
Connection cross section of access and exit with screws, for flexible conductor	1 / 25 mm ²
Type of connection	with screw

Equipment

Quick connect	no
With transparent product label holder	Yes

Standards

Standard text	IEC 60898-1
European directive WEEE	not concerned

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-25...70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I ² t	3
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-25...80 °C