



MW106

## MCB 1P 3kA C-6A 1M

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of poles	1 P
Type of pole	1 P
Fixing mode	DIN rail type O (symmetrical)
Curve	C

#### Functions

Concurrently switching N-neutral	No
----------------------------------	----

#### Configuration

Number of modules	1
-------------------	---

#### Connectivity

Top connection alignment for modular devices	Aligned terminal
Bottom connection alignment for modular devices	Aligned terminal

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	500 V
Max operating voltage	415 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated current	6 A
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 I <sub>n</sub>
Magnetic regulating current	5 / 10 I <sub>n</sub>
Rated short circuit breaking capacity I <sub>cn</sub> under 230V AC according IEC60898-1	3 kA
Rated short circuit breaking capacity I <sub>cn</sub> under 400V AC according IEC60898-1	3 kA

#### Electric current / temperature

Rating current -25°C	7.62 A
Rating current -20°C	7.45 A
Rating current -15°C	7.27 A

Rating current -10°C	7 A
Rating current -5°C	6.92 A
Rating current 0°C	6.75 A
Rating current 5°C	6.58 A
Rating current 10°C	6.4 A
Rating current 15°C	6.23 A
Rating current 20°C	6.05 A
Rating current 25°C	5.88 A
Rating current 30°C	6 A
Rating current 35°C	5.53 A
Rating current 40°C	5.35 A
Rating current 45°C	5.18 A
Rating current 50°C	4.81 A
Rating current 55°C	4.83 A
Rating current 60°C	4.66 A
Rating current 65°C	4.48 A
Rating current 70°C	4.31 A

#### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85

#### Dimensions

Depth of installed product	70 mm
Width of installed product	17.5 mm

#### Power

Maximum power loss per pole according to the product standard	3 W
Power loss per pole at In	1.19 W

#### Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

#### Installation, mounting

Type of top connection for modular devices	with screw
Tightening torque	2,8Nm
Type of Bottom Connection for modular devices	Blconnect

#### Connection

Connection cross-section at output with screw, for flexible conductor	1 / 25 mm <sup>2</sup>
Connection cross-section at output with screw, for massive conductor	1 / 35 mm <sup>2</sup>

Connection cross-section for rigid conductor, upstream terminals with screws	1 / 35 mm <sup>2</sup>
Connection cross-section of the access with screws, with flexible conductor	1 / 25 mm <sup>2</sup>
Type of connection	with screw
<b>Equipment</b>	
Can be accessorized	No
<b>Standards</b>	
Standard text	IEC 60898-1
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP20
REACH conform	No
<b>Use conditions</b>	
Operating temperature	-25...70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Altitude	2000 m
Storage/transport temperature	-25...80 °C
<b>temperatur</b>	
Temperature of calibration	30 °C