



RED114X



Switching relay 1gang with input flush-mounted 2-wire black

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Function switching

System functions function-related switching and control functions

Controls and indicators

Switching and control operations control by means of light, door release and comfort buttons of the indoor stations ; Door release buttons ; Buttons for impulse switch or stairway light timer activation ; potential-free button input to transmit a door release, light or storey call command via the bus

Voltage

Operating voltage over bus 22...26 V DC

Input voltage control input 12 V AC/DC

NO contact switching voltage max. 24 V

Electric current

No contact switching current max. 1 A

Materials

Colour black

Cable

Conductor Ø 0.5...0.8 mm

Settings

Device addressing rotary coding switch (one-man commissioning)

Use

System technology 2-wire

Software

Software version V2021

Use conditions

Operating temperature 5...40 °C

Storage/transport temperature -20...60 °C

Relative humidity (without condensation) 0...65 %