



REN101X



Call push-button module 1/1 with LED name plate built-in 2-wire modesta

Technical characteristics

Functions

Function	ringing
----------	---------

Controls and indicators

Call push-button	call button can be adjusted with light, door release or without function on the audio or video module ; call push-button with acknowledge tone (can be switched off on the audio or video module) and tactile feedback
Call push-button closing time	max. 3 s
Number of call buttons	1

Voltage

Operating voltage	24 V DC
-------------------	---------

Dimensions

Depth	19 mm
Distance mounting dowels (horizontal/vertical)	110 mm
Dimensions front plate (W x H x D)	120 x 120 x 2 mm
Dimensions name plate (W x D)	75.5 x 68.5 mm
Height	120 mm
Width of name plate insert	max. 0.3 mm
Width	120 mm
Material thickness stainless steel	2 mm

Materials

Colour of design line	Stainless steel
Colour	Stainless steel
Material / workmanship	metal brushed
Surface appearance	matt
Material / surface	stainless steel surface, brushed transversely

Equipment

Current name plate lighting	45 mA
-----------------------------	-------

Use

System technology	2-wire
-------------------	--------

Use conditions

Operating temperature	-20...55 °C
Storage/transport temperature	-30...80 °C

