



REN410X



AUDIO module built-in 2-wire stainless steel matt modesta

Technical characteristics

Architecture

Fixing mode	Built-in installation
-------------	-----------------------

Controls and indicators

Call push-button	Call push-button acknowledge tone can be switched off
Operating functions	door release during connection or at any time adjustable

Voltage

Operating voltage	24 V DC
Switching voltage door release contact	max. 24 V

Electric current

Switching current door release contact	max. 1 A
--	----------

Dimensions

Depth	21 mm
Recommended installation height	1.5 m
Dimensions front plate (W x H x D)	120 x 120 x 2 mm
Height	120 mm
Width	120 mm
Material thickness stainless steel	2 mm

Materials

Colour of design line	Stainless steel
Colour	Stainless steel
Material / workmanship	metal brushed
Material	stainless steel
Surface appearance	matt
Material / surface	stainless steel surface, brushed transversely

Cable

Conductor Ø	0.5...0.8 mm
-------------	--------------

Equipment

Door release unlocking time	1...10 s
Door release contact potential-free	max. 24V/1A
Loudspeaker unit	loudspeaker sound volume adjustable ; microphone sensitivity adjustable

Use

Use conditions

Operating temperature	-20...55 °C
Storage/transport temperature	-30...80 °C
Relative humidity (without condensation)	0...65 % (without condensation)