



REN410X



AUDIO module built-in 2-wire stainless steel matt modesta

Technical characteristics

Architecture

Fixing mode Built-in installation

Controls and indicators

Indication / display device configuration via LED display

Call push-button Call push-button acknowledge tone can be switched off

Operating functions door release during connection or at any time adjustable

Voltage

Operating voltage 24 V DC

Switching voltage door release contact max. 24 V

Electric current

Switching current door release contact max. 1 A

Dimensions

Depth 21 mm

Recommended installation height 1.5 m

Dimensions front plate (W x H x D) 120 x 120 x 2 mm

Height 120 mm

Width 120 mm

Material thickness stainless steel 2 mm

Materials

Colour of design line Stainless steel

Colour Stainless steel

Material / workmanship metal brushed

Material stainless steel

Surface appearance matt

Material / surface stainless steel surface, brushed transversely

Installation, mounting

Installation mode installation in surface-mounted or flush-mounted housings

Connection

Contact potential-free door release contact

Connection Connection for module connecting cable ; pluggable connection terminal block with screw terminals

Cable

Conductor Ø	0.5...0.8 mm
-------------	--------------

Settings

Setting	Volume, microphone sensitivity, door release function, camera and call button backlighting adjustable
---------	---

Equipment

Brightness	Operating modes of the call push-button module name plate backlighting adjustable: On, twilight controlled, Off
Cylinder	with error memory
Door release unlocking time	1...10 s
Door release contact potential-free	max. 24V/1A
Loudspeaker unit	loudspeaker sound volume adjustable ; microphone sensitivity adjustable

Use

System technology	2-wire
-------------------	--------

Safety

Protection	Loudspeaker and microphone protected against sabotage
------------	---

Use conditions

Operating temperature	-20...55 °C
Storage/transport temperature	-30...80 °C
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Main design line	Modesta
------------------	---------