



REQ002X



IK07 IP54

## Door station AUDIO 2/1 2-wire stainless steel matt one

### Technical characteristics

#### Architecture

Fixing mode flush-mounting or surface-mounting

#### Functions

Security functions privacy function

#### Compatibility

For labelling strip 12 mm

#### Controls and indicators

Call push-button call button can be adjusted with light, door release or without function ; call push-button with acknowledge tone (can be switched off) and tactile feedback

Call push-button closing time max. 3 s

Number of call buttons 2

Operating functions door release during connection or at any time adjustable

#### Voltage

Switching voltage door release contact max. 24 V

#### Electric current

Switching current door release contact max. 1 A

#### Dimensions

Depth 25 mm

Insertion depth 22.5 mm

Surface adjustment 17 mm

Dimensions front plate (W x H x D) 133.5 x 242 x 2 mm

Dimensions name plate (W x D) 75.5 x 14.5 mm

Dimensions name plate insert (W x H) 72.4 x 12 mm

Dimensions name plate insert (W x H x D) 72.4 x 12 x 0.14 mm

Height 242 mm

Width of name plate insert max. 0.5 mm

Width 133.5 mm

Material thickness stainless steel 2 mm

#### Materials

Colour of design line Stainless steel

Colour Stainless steel

Material stainless steel

|                                                   |                                                                                                                       |
|---------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Surface appearance                                | matt                                                                                                                  |
| Material / surface                                | stainless steel surface, brushed transversely                                                                         |
| <b>LED control</b>                                |                                                                                                                       |
| Operating voltage LED                             | 12 V AC                                                                                                               |
| LED operating current per call push-button module | 45 mA                                                                                                                 |
| <b>Installation, mounting</b>                     |                                                                                                                       |
| Installation mode                                 | for vertical mounting                                                                                                 |
| <b>Cable</b>                                      |                                                                                                                       |
| Conductor Ø                                       | 0.5...1.4 mm                                                                                                          |
| <b>Accessories included</b>                       |                                                                                                                       |
| Tool                                              | with opening tool                                                                                                     |
| <b>Equipment</b>                                  |                                                                                                                       |
| Door release unlocking time                       | 1...10 s                                                                                                              |
| Front plate                                       | front plate with non-visible opening mechanics and safety rope                                                        |
| <b>Use</b>                                        |                                                                                                                       |
| System technology                                 | 2-wire                                                                                                                |
| <b>Use conditions</b>                             |                                                                                                                       |
| Operating temperature                             | -20...55 °C                                                                                                           |
| Storage/transport temperature                     | -30...80 °C                                                                                                           |
| Relative humidity (without condensation)          | 0...65 % (without condensation)                                                                                       |
| <b>Instructions</b>                               |                                                                                                                       |
| Information text                                  | Caution! Do not aim the camera at direct light sources / sunlight, strong contrast or a highly reflective background. |