




MZ204



Shunt trip 24-48V AC 12-48V DC

Technical characteristics

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U_e	24 / 48 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	4000 V
DC control voltage	12 / 48 V
Command voltage AC	24 / 48 V
Rated operational voltage in DC	12 / 48 V

Electric current

$I_{min}=f(U=48V \text{ DC})$ for power circuit	0.55 A
---	--------

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	18 mm

Power

Inrush power absorbed	27 VA
Total power loss under I_N	24.3 W

Tripping

Time of response when opening	200 ms
Performance voltage / Tripping at U_e	50 %

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...60 °C
Air humidity protection	95%
Storage/transport temperature	-40...80 °C