



MZ212



## Over voltage release 230V AC

### Technical characteristics

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	AC
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	500 V
Microcut resistance	70 ms
Rated operational voltage in DC	0 V

#### Dimensions

Depth of installed product	68 mm
Height of installed product	87 mm
Width of installed product	17.5 mm

#### Power

Total power loss under IN	0.7 W
---------------------------	-------

#### Tripping

Time of response when opening	7 s
Performance voltage / Tripping at Ue	110 / 180 %

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	10000

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Operating temperature	-25...60 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C