



SBN225

## 2-pole, 25A Modular Switch

### Technical characteristics

#### Architecture

Type of order	Break switch
Neutral position	without neutral
Number of poles	2 P
Type of pole	2 P

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	440 V
Type of voltage input 1	AC
Rated impulse withstand voltage	4000 V

#### Electric current

Rated operational current in AC21 category B	25 A
Acceptable current rating with AC22 category A	25 A
Rated current	25 A
Rated short-time withstand current 1s	0.375 kA
Thermal rated current outside of housings	25 A
Rated operational current in AC21 category A	25 A
Acceptable current rating with AC22 category B	25 A

#### Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under IN	1.8 W
Power loss per pole at In	0.9 W

**Endurance**

---

Electrical durability at nominal load in AC21 in operating cycles	25000
Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000

---

**Installation, mounting**

---

Tightening torque	1,8Nm
-------------------	-------

---

**Connection**

---

Connection cross-sect. flexible conductor	1,5 / 10mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 16mm <sup>2</sup>
Cage clamp position	off set
Type of connection	with screw

---

**Equipment**

---

Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0

---

**Standards**

---

Standard text	IEC 60947-3 ; IEC/EN 60669-2 ; IEC/EN 60669-4
---------------	---

---

**Safety**

---

Halogen free	No
--------------	----

---

**Use conditions**

---

Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-40...80 °C

---