



SBN263N

## 2-pole, 63A Modular Switch

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of poles	2 P
Type of pole	2 P

#### Configuration

Number of modules	2
-------------------	---

#### Main electrical features

Rated operational voltage Ue	415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	6000 V

#### Electric current

Rated operational current in AC21category B	63 A
Acceptable current rating with AC22 category A	63 A
Rated current	63 A
Rated short-time withstand current 1s	0.945 kA
Thermal rated current outside of housings	63 A
Rated operational current in AC21 category A	63 A
Acceptable current rating with AC22 category B	63 A

#### Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under I <sub>N</sub>	4.6 W
Power loss per pole at I <sub>N</sub>	2.3 W

#### Endurance

Electrical durability at nominal load in AC21 in operating cycles	5000
Electrical durability at nominal load in AC22 in operating cycles	5000
Number of mechanical operations	60000
<b>Installation, mounting</b>	
Tightening torque	2,8Nm
Top removability for modular devices	No
Bottom removability for modular devices	No
<b>Connection</b>	
Cage clamp position	in line
<b>Equipment</b>	
Quantity of NO contacts	2
Can be accessorized	Yes
<b>Standards</b>	
Standard text	IEC 60947-3
European directive WEEE	not concerned
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-20...50 °C
Altitude	2000 m
Storage/transport temperature	-40...80 °C