



RED113X



IP20

Switching relay 2gang RMD i2Audio light grey

Technical characteristics

Functions

Function	switching
System functions	subscriber-related switching and control functions

Compatibility

Compatibility	for information on indoor stations that can be used, see notes in the operating instructions
---------------	--

Controls and indicators

Control	Activation via door call, storey call and/or internal call ; Activation via a BSR-200 switching relay
Switching and control operations	Door release buttons ; Buttons for impulse switch or stairway light timer activation ; control by means of light, door release and comfort buttons of the indoor stations

Voltage

Operating voltage over bus	22...26 V DC
NO contact switching voltage	max. 24 V

Electric current

No contact switching current	max. 1 A
------------------------------	----------

Dimensions

Width of rail mounted device (RMD)	3 modules
------------------------------------	-----------

LED control

LED	with status LEDs for switching contacts
-----	---

Installation, mounting

Installation mode	Rail mounted unit (RMD)
-------------------	-------------------------

Connection

Bus connection	i2BUS audio
Connection	two potential-free relay switching contacts (NO contact)

Cable

Conductor Ø	0.5...0.8 mm
-------------	--------------

Settings

Device addressing	rotary coding switch (one-man commissioning)
-------------------	--

Use

Software

Software version	V2020
------------------	-------

Safety

REACH conform	No
---------------	----

Halogen free	No
--------------	----

Use conditions

Operating temperature	5...40 °C
-----------------------	-----------

Storage/transport temperature	-20...60 °C
-------------------------------	-------------

Relative humidity (without condensation)	0...65 %
--	----------

Identification

Main design line	T electronics
------------------	---------------