



ST315



## Safety transformer 63VA 230V12-24V

### Technical characteristics

#### Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

#### Configuration

Number of modules	6
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	4000 V
Output voltage 2	24 V
Open circuit voltage secondary	14.2 / 26.5 V
Output voltage	12 / 24 V

#### Electric current

Output intensity 2	2.63 A
Output intensity	5.25 A

#### Dimensions

Depth of installed product	68 mm
Height of installed product	85 mm
Width of installed product	105 mm

#### Power

Power consumed	63 VA
Total power loss under IN	4.5 W

#### Installation, mounting

Suitable for surface mounting	Yes
Suitable for flush-mounting	No
Mounting type	din-Rail

#### Cable

Max. cable length to door actuator release 0.5 A	max. 100 m
Max. cable length to door actuator release 1 A	max. 50 m

#### Equipment

On/Off switch	No
---------------	----

Short-circuit protected

Yes

---

**Standards**

---

Standard text

EN 61558-2-6

---

European directive WEEE

concerned

---

**Safety**

---

Protection index IP

IP20

---

Temperature protection

Yes

---

**Use conditions**

---

Operating temperature

-20...35 °C