



RED321X



**IP20**

## Output coupler flush-mounted 2-wires

### Technical characteristics

#### Functions

|                  |  |
|------------------|--|
| Function         | extending                              |
| System functions | decoupling of an i2BUS audio bus cable |

#### Attenuation

|                   |      |
|-------------------|------|
| Transmission loss | 0 dB |
|-------------------|------|

#### Installation, mounting

|                   |  |
|-------------------|--|
| Installation mode | for installation in flush-mounted wall box |
|-------------------|--|

#### Connection

|                |   |
|----------------|---|
| Bus connection | 2-wire, for video door stations ; 2-wire, for video indoor stations ; i2BUS audio, for audio components |
|----------------|---|

#### Cable

|             |              |
|-------------|--------------|
| Conductor Ø | 0.5...0.8 mm |
|-------------|--------------|

#### Use

|                    |  |
|--------------------|--|
| System technology  | i2 Audio   |
| Video distribution | bus cable 1x incoming in 1x outgoing, 1x audio branching off ; unwired terminals must be completed with terminator |

#### Software

|                  |       |
|------------------|-------|
| Software version | V1000 |
|------------------|-------|

#### Safety

|              |    |
|--------------|----|
| Halogen free | No |
|--------------|----|

#### Use conditions

|  |             |
|--|-------------|
| Operating temperature                    | 5...40 °C   |
| Storage/transport temperature            | -20...60 °C |
| Relative humidity (without condensation) | 0...65 %    |

#### Identification

|                  |               |
|------------------|---------------|
| Main design line | T electronics |
|------------------|---------------|