



RED612X



IP20

Distributor/branch 2 ways RMD 2-wires

Technical characteristics

Functions

| | |
|------------------|------------------------------|
| Function | distributing |
| System functions | distribution of single lines |

Dimensions

| | |
|------------------------------------|-----------|
| Width of rail mounted device (RMD) | 1 modules |
|------------------------------------|-----------|

Attenuation

| | |
|--------------------------|------|
| Distribution attenuation | 3 dB |
|--------------------------|------|

Installation, mounting

| | |
|-------------------|-------------------------|
| Mounting type | din-Rail |
| Installation mode | Rail mounted unit (RMD) |

Connection

| | |
|----------------|---|
| Bus connection | 2-wire, for video door stations ; 2-wire, for video indoor stations |
|----------------|---|

Cable

| | |
|-------------|--------------|
| Conductor Ø | 0.5...0.8 mm |
|-------------|--------------|

Use

| | |
|--------------------|---|
| System technology | 2-wire |
| Video distribution | for distributing the incoming bus cable to the outgoing one ; for coupling the incoming bus cables to the outgoing ones ; unwired terminals must be completed with terminator |

Software

| | |
|------------------|-------|
| Software version | V1000 |
|------------------|-------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |

Use conditions

| | |
|--|-------------|
| Operating temperature | 5...40 °C |
| Storage/transport temperature | -20...60 °C |
| Relative humidity (without condensation) | 0...65 % |

Identification

| | |
|------------------|---------------|
| Main design line | T electronics |
|------------------|---------------|