



SVN123

Orange LED Indicator light 230VAC

Technical characteristics

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U_e	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

Dimensions

Depth of installed product	62 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	0.8 W
---------------------------	-------

Lighting control

Type of lamp	LED
--------------	-----

Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	0,75 / 6mm ²
Connection cross-sect. rigid cable	0,75 / 10mm ²
Lamp socket type	Fix
Type of connection	with screw

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3

Altitude

2000 m

Storage/transport temperature

-40...80 °C